

Roof outlet filter, Extract: W: 223 mm, H: 223 mm, RAL 7035, IP54,



Model		
product brand name	SIVACON	
product designation	outlet filter for roof mounting	
type of ventilation	ventilation	
fan design withdrawable fan	No	
design of the product EMC version	No	
General technical data		
cutout width	223 mm	
cutout height	223 mm	
Protection class		
protection class IP	IP54	
Appearance		
color	light grey	
Product details		
product component fan	Yes	
Mechanical Design		
height	287 mm	
width	287 mm	
depth	85 mm	
fastening method	snap-on mounting	
fastening method		
• 19-inch installation	No	
• wall mounting	No	
net weight	0.7 kg	
material	plastic	
ambient temperature during operation		
• minimum	-10 °C	
• maximum	55 °C	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-5VE45>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-5VE45>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-5VE45

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

