

Eaton 100MJ27-7

Catalog Number: 100MJ27-7

Eaton Bussmann series low voltage british standard fuse, 100A, AC 415 V, V88/J, 31 x 112 mm, gU, type 7



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	100MJ27-7
	EAN
	5027590427838
Product Length/Depth	Product Height
120 mm	63 mm
Product Width	Product Weight
158 mm	154 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269
	EAC

Electrical data

Amperage Rating

100 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

80 kA

Class

Class gG/gL

Product specifications

Application

feeder pillars

Fuse type

MJ27

Connection

Bolt-on

Resources

Catalogs

[CA134002EN](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical service bulletins

[Datasheet - 100MJ27-7](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)