



Part Number : [2144151001](#)

Product Description : 2.4GHz Wi-Fi/Bluetooth
Hinged External Antenna, with SMA Male Connector,
White

Series Number : 214415

Status : Obsolete

Product Category : Antennas

Documents & Resources

Drawings

[2144151001_sd.pdf](#)

[2128600001-PK1.pdf](#)

Specifications

[2144150001-AS.pdf](#)

[2144150001-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Antennas
Series	214415
Description	2.4GHz Wi-Fi/Bluetooth Hinged External Antenna, with SMA Male Connector, White
Component Type	External Antenna
Function	Signal
Product Name	2.4GHz Wi-Fi/BT Antenna
Protocol	BT, Wi-Fi
Type	External
UPC	193264434749

Electrical

Band#1 F_End (MHz)	2500
Band#1 F_Start (MHz)	2400
Electrical Connectivity	Cable
Peak Gain (dBi)	5.3 @ 2.4 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>80% @ 2.4 GHz

Physical

Length	108.40mm
Mounting Style	N/A
Net Weight	7.715/g
Packaging Type	PET Bag
Polarization	Linear

Radiation Pattern	Omnidirectional
Width	9.35mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	SMA Female Receptacle

This document was generated on Nov 06, 2025

Obsolete