

General Information

Extended Product Type:	OHM125L12
Product ID:	1SCA022739R1150
EAN:	6417019308616
Catalog Description:	Handle OHM125L12
Long Description:	Stainless steel handles, indication I-O/ON-OFF, padlockable with 3 padlocks in the OFF-position, door interlock in the ON-position, IP66 (NEMA 4X), grey.

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019308616
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	160 mm
Product Net Height:	69 mm
Product Net Depth:	51 mm
Product Net Weight:	2 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	125 mm
Package Level 1 Height:	69 mm
Package Level 1 Length:	90 mm
Package Level 1 Gross Weight:	2 kg
Package Level 1 EAN:	6417019308616

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Handle Length:	125 mm
Handle Type:	Pistol
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHM125
Product Name:	HANDLE
Suitable For:	OS315-400 & OT630-800
Suitable for Product Class:	Switches

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5.0:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

