

Pressure transmitter Model A-10
Type A-10
Item no.: 48450472

MEASURING RANGE	
Measuring range	0...1 bar abs
Overpressure limit	3 times
Vacuum tightness	yes
OUTPUT SIGNAL	
Output signal	0 ... 10 V, 3-wire
Permissible load in Ω	> maximum output voltage / 1 mA
Settling time	< 1 ms
POWER SUPPLY	
Power supply	14...30 V DC
Total current consumption	max. 8 mA
ACCURACY INFORMATION	
Non-linearity	0.5% BFSL
Accuracy at room temperature	$\leq \pm 1.0$ % of span
Measuring deviation of the zero signal	$\leq \pm 0.5$ % of span
Long-term drift	$\leq \pm 0.1$ % of span
TEMPERATURE ERROR	
	typ. 1 %, max. 2.5 %
OPERATING ENVIRONMENT CONDITIONS	
Permissible medium temperature	0...+80 °C
Permissible ambient temperature	0 ... 80 °C
Vibration resistance	10 g (IEC 60068-2-6, under resonance)
Shock resistance	500 g (IEC 60068-2-27, mechanical)
Service life	100 million load cycle
MATERIALS	
Wetted parts	Stainless steel 316L
Non-wetted parts	Stainless steel 316L, HNBR, PA
PROCESS CONNECTION	
Process connection	G 1/4 B
Sealing	stainless steel
ELECTRICAL CONNECTION	
Electrical connection	valve connector, size A
Ingress Protection	IP65
pin assignment	UB=1, 0V=2, S+=3
ELECTRICAL SAFETY	
Short-circuit resistance	S+ vs. U-
Reverse polarity protection	U+ vs. U- (no reverse polarity protection with ratiometric output signal)
Insulation voltage	DC 500 V
CE-CONFORMITY, APPROVALS AND CERTIFICATES	
CE conformity	PED 2014/68/EU
Approvals	cULus

