

CW-T6**IP68 | IP69K | MIL-STD-810H****SERVICES IN FRANCE**

RUGGED SMARTPHONE

THIN, POWERFUL, AND BUILT TO WITHSTAND ANYTHING

- Unisoc Tiger T606 Processor
- Android 13
- Resistant to drops up to 1.2m
- IP68, Tumble tested 1000 times at 1m
- Standard 6300mAh Battery
- NFC Reader
- 4G Dual SIM



SOFTWARE	Android 13	WIRELESS	4G GPS / Glonass / Beidou / Galilée Wi-Fi 802.11a/b/g/n/ac Bluetooth® 5.0
DURABILITY	MIL-STD-810H (multiples drops 1.2 m) IP68 Tumble test 1000 times x 1m	POWER SUPPLY	Standard Battery: 6 300mAh
CPU	Unisoc Tigre T606 Octo Core, 2*1,6 GHz-Cortex-A75 6*1,6 GHz-Cortex-A55	SECURITY	NFC reader
MEMORY	4GB	SENSORS	9-Axis MEMS Sensors (Accelerometer, Compass, Gyroscope) Ambient Light Sensor Proximity Sensor
STORAGE	128GB	DIMENSIONS	81.5mm x 166.4mm x 15.4mm
DISPLAY	5.93", resolution 720*1440, 440 nits	WEIGHT	300 g
INTERFACES	USB Type-C Port, OTG Support 3.5mm Audio Jack MicroSD Card Slot		
CAMERA	Front Camera: 5MP Rear Camera: 20MP		

