

# VARTA Aluminium Light F10 Pro 2AAA with Batt.



Elegant flashlight with black anodized aluminium housing and silver ring in matte finish with 3 light modes, high lumen output and long runtimes.



## Information

- Precision focus (Infinitely focusable light beam spot-to-flood)
- Anodized aluminium body
- Textured housing surface for maximum grip
- 3 light modes: high, low, strobe
- Shock proof (1 m)
- Rear mechanical switch
- High performance LED

## Article Details

Ordernumber	16606 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	45.00 m
Runtime	25 h
Total light output	150 lm
Product Diameter mm	20.00
Product Length / Depth mm	133.00
Product Weight g	36.80

## Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 056422	80.00	17.00	195.00	0.07
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	6	40 08496 056675	208.00	90.00	95.00	0.46
PAL (Pallet)	3036	40 08496 056682	800.00	1,200.00	1,195.00	254.47
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
11	46		506		6	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany  
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

