



PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:56 (UTC)



6008ZZ

Single-Row Deep Groove Ball Bearings

Parts Number

6008ZZC3

Boundary Dimensions

d	40	mm	Bore diameter
D	68	mm	Outside diameter
B	15	mm	Width
r (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	18400	N	Basic dynamic load rating
C0r	11500	N	Basic static load rating

Speeds

Grease	12000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	45	mm	Diameter of shaft abutment
da (max.)	47.5	mm	Diameter of shaft abutment
Da (max.)	63	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	15.3	Factor
----	------	--------

Additional information

z	12	Number of Balls	
Dw	7.938	mm	Ball Diameter

Mass

Mass approx.	0.19	kg	Mass approx.
--------------	------	----	--------------

