

3114 19

Crowfoot spanner

| | |
|-----------------------|-------------|
| Code | ETIM |
| 6670480 | EC002130 |
| EAN | UNSPSC |
| 4010886667040 | 27-11-17-06 |
| Country of origin | eCl@ss |
| Germany | 21-04-01-90 |
| Customs tariff number | |
| 82041100 | |



Article description

- Angled open-end wrench for working in hard-to-reach areas
- Vanadium steel 31CrV3, chrome-plated
- No. 3114 = Delivery without pivot pin
- No. DS 3114 = supplied with rotary pin 26 D

Article information

| | | | |
|--------------------------|--|---------------------------|----------|
| Contents (Qty of pieces) | 1 | Width across flats l [mm] | 19 |
| Net weight [kg] | 0,224 kg | Head height l [mm] | 7 mm |
| Total length [mm] | 200 mm | Width of head l [mm] | 37,0 mm |
| Surface | chrome-plated | Shaft diameter | 19,6 mm |
| Use | For working in extremely difficult to access areas | Tommy bar-Ø 1 | 12 |
| Material | 31CrV3 | Diameter l [mm] | 12,00 mm |
| Bore Ø [mm] | 13 mm | | 12,5 |