

31 KR 30-60

Friction ratchet handle with insert ring

Bi-hexagon UD profile or bi-hexagon

Code	ETIM
6256980	EC011810
EAN	UNSPSC
4010886625699	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



Article description

- Friction spanner (31 K) with exchangeable UD profile or bi-hexagon insert rings (31 R)
- Hexagonal rings available on request
- Especially suitable for steel and scaffolding construction
- Up to 30" flat shaft, from 35" with slip-on tube
- Vanadium steel 31CrV3, manganese-phosphated
- Explanation of the article number: 31 KR 16-32 = ratchet 31 K 16" and insert ring 31 R 32 mm

Article information

Contents (Qty of pieces)	1	Head height 1 [mm]	33,5 mm
Net weight [kg]	2,879 kg	Width of head 1 [mm]	92,0 mm
Total length [mm]	760 mm	Total length [inch]	30
Surface	manganese phosphated	Ring profile	UNIT-DRIVE
Material	Chrome-vanadium steel 31CrV3	Insert ring double hexagon	60