



Part Number : [2064621000](#)
Product Description : Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 10 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Series Number : 206462
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

- [2064621000_sd.pdf](#)
- [2064620000-PK-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2064600001-AS-000.pdf](#)
- [2064600000-PS-000.pdf](#)
- [2159530000-PS-000.pdf](#)
- [2064600000-TS-000.pdf](#)
- [2064600001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	206462
Description	Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 10 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance
Product Name	Micro-Fit+
UPC	191130009145

Agency

UL	E29179
----	--------

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural

Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.187/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>