

29109

# Table & Floor Scraper, 260 mm, Black



Remove stubborn food debris from floors and other surfaces with this Table and Floor Scraper. Features a stainless-steel blade and can be used with any Vikan handle.

# Technical Data

<b>Item Number</b>	29109
<b>Blade Thickness</b>	1 mm
<b>Material</b>	Polypropylene Stainless Steel (AISI 304)
<b>Complies with (EC) 1935/2004 on food contact materials<sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	800 Pcs.
<b>Quantity Per Layer (Pallet)</b>	80 Pcs.
<b>Box Length</b>	320 mm
<b>Box Width</b>	270 mm
<b>Box Height</b>	130 mm
<b>Length/Depth</b>	260 mm
<b>Width</b>	175 mm
<b>Height</b>	30 mm
<b>Gross Weight</b>	0,28 kg
<b>Net Weight</b>	0,26 kg
<b>Cubik metre</b>	0,0014 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. usage temperature (for food contact)</b>	170 °C
<b>Max usage temperature (non food contact)</b>	170 °C
<b>Min. usage temperature<sup>3</sup></b>	-20 °C
<b>Max. drying temperature</b>	120 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705020291098
<b>GTIN-14 Number (Box quantity)</b>	15705020291095
<b>Commodity Code</b>	82159910
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.