




## ACCESSORIES


### OTHER ACCESSORIES

#### FOR CAT II & LOWER INSTALLATIONS



Modèle	Description
	<b>SHT40KV high-voltage probe for multimeters</b> <b>P01102097</b> Maximum rated voltage: 40 kVdc, 28 kVRMS or 40 kVPEAK (50/60 Hz) Division ratio (input/output): 1 kV / 1 V For multimeters with 10 MΩ input impedance



#### EXTERNAL POWER SUPPLY & MAINS POWER PACK

Model	Description
	<b>Set of 4 x 1.5 V LR06 rechargeable batteries with low self-discharge plus charger</b> <b>HX0053</b>
	<b>Set of 4 x 1.5 V LR06 rechargeable batteries with low self-discharge</b> <b>HX0051B</b>



Model	Description
	<b>230 V / μUSB mains adapter – B</b> <b>P01651023</b> • 110 – 240 V 50/60 Hz • Female USB type A, 5 V 1 A Charging and connection cable • Male USB type A – Male USB type μ-B • 1.8 m


#### TEMPERATURE AND ROTATION SPEED MEASUREMENT PROBES

Model	Description
	<b>C.A 1711</b> <b>P01102082</b> Tachometer probe - Pulse output $\frac{1.1V}{0}$ / rev. - 2 insulated banana plugs Ø 4 mm - Measurement range: 6 to 120,000 RPM - IP 53
	<b>C.A 801</b> <b>P01652401Z</b> Temperature adapter for multimeters - -40 °C to +1,000 °C - 1 mVDC / °C (or /°F) Delivered with 1 K sensor and 1 battery

Model	Description
	<b>C.A 1871</b> <b>P01651610Z</b> Infrared sensor Compatible with any multimeter equipped with an mV range - Measurement range: -30 °C to +550 °C - Output: 1 mV/1 °C - Distance/spot ratio: 8/1 - Accuracy: ± 2 %
	<b>C.A 803</b> <b>P01652411Z</b> Temperature adapter for multimeters - 2 measurement channels - -40 °C to +1,000 °C - 1 mVdc / °C (or /°F) - Ø1 - Ø2 differential measurement Delivered with 2 K sensors and 1 battery

#### ADAPTERS FOR TEMPERATURE MEASUREMENT SENSORS

Modèle	Description
	<b>Set of 2 safety thermocouple adapters for multimeters</b> <b>P01102106Z</b> Female thermocouple plug – insulated red/black male plugs Ø 4 mm with 19 mm spacing
	<b>Safety adapter and K-sensor temperature probe</b> <b>P01102107Z</b> For multimeters and multimeter clamps equipped with a temperature measurement calibre with 19 mm-spaced banana inputs - Measurement range from -50 °C to +350 °C - Sensor length: approx. 100 cm

Modèle	Description
	<b>Pt100/Pt1000 sensor adapter for multimeters</b> <b>HX0091</b> Female Pt100/Pt1000 plug – Red/black insulated male plugs Ø 4 mm