

FEATURES

- Voice:Tests RJ-11/12 6-wire cables
- Data:Tests RJ-45 8wire cables
- Video:Tests F-Connector Coax Cables
- Tone Generator
- Cable Identification
- Shield Detection
- Voltage Warning
- Low Battery Indication
- Auto Power Off

RS PRO Network Cable Tester

RS Stock No.: 241-3189



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS-VDV100 the Professional VDV Wire Tester analyzes wiring on phone, computer network and coax cables in one easy step.

The large backlit LCD display maps out connections and describes wiring faults.

The built-in tone generator and the included Video and Data remote identifiers can be used to quickly locate cables in wiring closets and patch panels.

With proper use, this tester will provide many years of reliable service.

General Specifications

| Model Number | RSVDV-100 |
|-----------------------------------------------------|------------------------------------------------------------------------------------------|
| Maximum Coax Cable Length | 1000 feet (305m) |
| Minimum Cable Length for Split Pair Detection | 1.6 feet (0.5m) |
| Maximum Coax Cable Resistance | 100 ohms maximum DC |
| Humidity | 10% to 90%, non-condensing |
| Operating Temperature | 0 to 50°C (32 to 122°F) |
| Storage Temperature | -20 to 60°C (-4 to 140°F) |
| Maximum Voltage Between any two Pins Without Damage | 60V DC or 55V AC |
| Display type | LCD |
| Cable Types | 4Shielded or Unshielded: Cat 7, Cat 7a, Cat 6a, Cat 6, Cat 5e, Cat 5, Cat 4, Cat 3, Coax |



Electrical Specifications

| Power Source | Battery |
|------------------|-------------------------------------------------|
| Battery Included | Yes |
| Battery Type | AA |
| Battery Life | 30H |
| Accessories | Two "AA" batteries, gift box with carrying case |

Mechanical Specifications

| Dimensions | 152mm x 61 mmx 34 mm |
|------------|----------------------|
| Length | 152mm |
| Width | 61mm |
| Height | 34mm |
| Weight | 230g |

Additional Information

| Custom Tariff Number | 9030339000 | |
|----------------------|------------|--|

Approvals

| Compliance/Certifications | CF |
|---------------------------|----------|
| | <u> </u> |