

Technical data sheet

Article number:
924-00432

QDF2-5/8

Product Group	Quick Connect Female Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC), Copper (CU)
Colour	Blue (BU)

Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	4.9 mm
Length (L)	20 mm
Length (L2)	11 mm
Length (L3)	9 mm
Max Current	15 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	5 mm

