

Features

- Conforms to ANSI/TIA-568.2-D & ISO/IEC 11801-1
- HDPE Insulation
- Backwards Compatible to CAT 3 & CAT 5
- U/UTP
- Operation Temp -20c - 60c
- Conductor DC Resistance $\leq 11.7 \Omega$ /100m

RS PRO Ethernet Cable

RS Stock No.: 0199198



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Premium VLZ design for optimal audio performance. The RS Pro Unterminated Cat5e type cables have primary application use for both home and office computer networks. This cable is compliance with CE, UKCA, RoHS, and REACH standards. It offers an IP67 rating, ensuring excellent protection from water and dust ingress. This cable features 8 core strands with LSZH fire behaviour, making it suitable for environments where low smoke emissions are critical. With solid conductor strands and a 24 AWG, it combines safety and reliability in its design.

General Specification

LAN Category	Cat5e
Length	305m
Terminated/Unterminated	Unterminated
Shield Type	None
Shielded/Unshielded	Unshielded
CPR Certification	Eca
Coding	T568B
Sheath Colour	Violet
Outer Sheath Material	LSZH
IP Rating	IP67
Core Strands	8
Fire Behaviour	LSZH

Voltage Rating	300V
Conductor Strand Type	Solid
American Wire Gauge	24AWG
Cable Shape	Round
Number of Strands	8
Outer Diameter (mm)	4.9mm
Cross Sectional Area (mm)	0.1885mm
Current Rating (A)	3.5A
Applications	Cat5e type cables have primary application use for both home and office computer networks