

Features

- Durable black ABS carry case with precision-cut foam insert for secure storage.
- High-quality taps and dies for accurate, cleaning threading.
- Includes both taper and bottoming taps for versatility.
- Complete with matching tap wrenches and die stocks.

RS PRO Tap & Die Set



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro Tap and Die set is supplied in a durable black ABS case with foam insert and includes high-quality taper and bottoming taps, matching dies, and the appropriate tap wrenches and die stocks. Sets are available in metric ranges (M2-M6 and M6-M12) and UNC range (1/4-1/2 and 1/4-3/4), providing a versatile solution for cutting repairing, and maintaining internal and external threads.

General Specifications

Brand	RS PRO
Product Type	Thread Tap & Die Set
Maximum Die Size	M6, M12, ½ UNC, ¾ UNC
Minimum Tap Size	M2, M6, ¼ UNC, ½ UNC
Maximum Tap Size	M6, M12, ½ UNC, ¾ UNC
Minimum Die Size	M2, M6, ¼ UNC, ½ UNC
Set Contents	Taps & Dies
Material	High Speed Steel (HSS)

Stock No.	Brand	Set Range	Sizes Included
879461	RS PRO	M2 - M6	M2, M3, M4, M5, M6
879460	RS PRO	M6 - M12	M6, M7, M8, M9, M10, M11, M12
879462	RS PRO	1/4 - 1/2 UNC	1/4, 5/16, 3/8, 7/16, 1/2
879463	RS PRO	1/4 - 3/4 UNC	1/4, 5/16, 3/8, 7/16, 1/2, 5/8, 3/4