


E.2015 | DIGITAL HEAT GUN



Description :

- On / Off button easy to use with two modes: - Mode 1: 250 l/min – (50°-400°). - Mode 2: 500 l/min – (50°-600°).
- Durable and powerful 2000 Watt motor.
- Excellent control with wide LCD screen facilitating temperature configuration.
- Compact and light tool with a gun handle for easy use.
- Overheating protection: The heating element desactivates automatically for a few seconds when overheating, period during which the tool continues producing fresh air.
- Wired tool for socket of the Europe 220-240 V / 50 Hz type.
- Ready to use: Distribution nozzle and reflector nozzle supplied with the tool.
- Max power : 2000 W.
- Power supply: 220-240 V/50 Hz.
- Air flow rate (2 speeds): 250 l/min and 500 l/min.
- Supplied with 2 nozzles: E.2002B1 - E.2002B3.
- E.2002B1: Distribution nozzle, dim. (L. x h x d): 75 x 75 x 33.7 mm; weight 58 g.
- E.2002B2: Cross-flow nozzle, dim. (L. x h x d): 75 x 80 x 33.7 mm; weight 56 g.
- E.2002B3: Reflector nozzle, dim. (L. x h x d): 33 x 60 x 33.7 mm; weight 32 g.
- E.2002B4: Concentrator nozzle, dim. (L. x h x d): 20 x 52 x 33.7 mm; weight 30 g.

Informations :

	E.2015
H [mm]	210
Width l [mm]	72
L [mm]	250
[g]	980