

PRODUCT-DETAILS

TC112-TB

MINI MTG BASE .75X.37IN NAT NYL SCR



General Information

Extended Product Type	TC112-TB
Product ID	7TAG009880R0004
EAN	5414363058052
Catalog Description	MINI MTG BASE .75X.37IN NAT NYL SCR
Long Description	Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.75 Inches), Width of 9.5mm (0.374 Inches), Height of 4.8mm (0.189 Inches), Fillister-Head Screw Mounting Method

Ordering

EAN	5414363058052
UPC	786210822587

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	8.5 in 216 mm
Package Level 2 Height	7.6 in 193 mm
Package Level 2 Depth / Length	16.3 in 414 mm

Additional Information

Brand / Label	Ty-Rap
Cable Size	0.19 in 4.82 mm
Color	Natural
Effective Date	19670831
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Mounting Base
Special Functions	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC112-TB
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC112-TB
REACH Declaration	9AKK107992A3995
RoHS Information	9AKK107992A8806

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

