

## M23 ComLock-S Hood 7-12 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 0482
Specification	M23 ComLock-S Hood 7-12 mm
HARTING eCatalogue	<a href="https://harting.com/09151000482">https://harting.com/09151000482</a>

### Identification

Category	Hoods / Housings
Series	Circular connectors M23
Identification	Signal
Type of hood/housing	Cable housing
Description of hood/housing	EMC version

### Version

Size	M23
Version	Top entry
Locking type	ComLock-S rapid locking
Details	Compatible to Speedtec (TE)

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	7 ... 12 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	89.4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140184053
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405