



WT1010H (UK) 230V

Item No: T0053438399N

1-Channel Soldering Station Set, 150 W with soldering iron WP120

KEY FEATURES

- + Power unit WT1H, 1 channel with soldering iron WP120 Robust and safety rest WSR201
- + WP120 (120 W): All-rounder with Power-Response soldering tip, XT Tip family and XT soldering head
- + High productivity (Power unit with 1 channel, 150W)
- + Intuitive use thanks to clear menu structure
- + Reduced footprint thanks to stackability
- + Graphical backlit LC-Display
- + High performance and functionality - many connectable tools
- + Automatic standby of tool thanks to integrated acceleration sensor in the tool
- + Housing cover useable as storage
- + OFF time, Prozess window, Lock function, Offset

TECHNICAL DATA

Length	149mm
Dimensions L x W x H	150 x 130 x 101 mm
Equipotential Bonding Socket	Via 3.5mm pawl socket on front of device
ESD Safe	Yes
Interface	One Switching Output
Number of Channels	1
Power	150 W
Temperature Accuracy °C	± 9°C
Temperature Accuracy °F	± 17°F
Temperature Range (Depends on Tool)	Adjustable from 50°C - 550°C (150°F - 950°F) Adjustable temperature range varies among tools
Temperature Range °F	150 - 950 °F
Temperature Stability °C	± 2°C
Temperature Stability °F	± 4°F
Voltage	230V (50 Hz)
Product Family	WT Line Soldering Stations