

EK EKOE 130 T



Sample photo

Order symbol: EKOE 130 T
Product nbr: 2538137
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074013835
EI. number:
 Finland: 3425468
 Electric No. Italy: 7502040
 Electric No. Sweden: 2538137

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	280	280	130	EKO 30-G	Cover
inch:	11.0	11.0	5.1	EKO 80-G	Cover
Materials:				EKO 30-T	Cover
Material:	Polycarbonate			EKO 80-T	Cover
Base colour:	RAL 7035 -light grey			EKOVT	Mounting plate
Cover screws material:	Polyamide			EKOXT	Mounting plate isolated
Cover colour:	Clear transparent			EKV 22	DIN-35 Mounting rail
Cover screws colour:	Grey			EKOZR	Extension frame
Gasket material:	Polyurethane			Rating:	
Temperatures:				Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (short term):	-40 ... 120 °C			Impact Resistance (EN 62262): IK08	
Temperature °C (continuous):	-40 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 250 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (continuous):	-40 ... 175 °F			UV resistance: UL 508	
Accessories:				Flammability Rating: UL 746C 5"	
EKOE	Base, PC			Glow Wire Test (IEC 695-2-1) °C: 960	
Certificates:				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
				SGS Fimko	
				Gost R	

