

Technical data sheet

Article number:
111-15719

T150LL



Product Group	Cable Ties Polyamide 6.6 standard
Product Family	T-Series in PA66 natural
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)
Application Tool	ProCut 9 no battery, MK9P, MK9P w/ Upper air, MK10-SB, EVO9, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Ø max.	274.3 mm
Bundle Ø min.	8.0 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	925.0 mm
Min.Tensile Strength	780 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	25 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL 62275
Thickness (T)	2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
Variant	Inside Serrated
Weight/Unit	0.016761 kg
Width (W)	8.9 mm

