



6207DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6207DDUC3

Boundary Dimensions

d	35	mm	Bore diameter
D	72	mm	Outside diameter
B	17	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	28200	N	Basic dynamic load rating
C0r	15300	N	Basic static load rating

Speeds

Grease	6300	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	41.5	mm	Diameter of shaft abutment
da (max.)	44.5	mm	Diameter of shaft abutment
Da (max.)	65.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	13.8	Factor
----	------	--------

Additional information

z	9	Number of Balls	
Dw	11.112	mm	Ball Diameter

Mass

Mass approx.	0.284	kg	Mass approx.
--------------	-------	----	--------------

