

Features

- Medium Duty
- Stainless Steel
- Industrial castor
- Rotation Swivel
- Fixing Hole
- Polyurethane
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0730050



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Polyamide 6 wheel coated with injection polyurethane DESMOPAN® (Bayer®) 97 Shore A. Hub on stainless steel roller bearing. In pressed stainless steel AISI 304 turning on double rim of balls in stainless steel AISI 420. Assembled with self-locking nut.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity (Kg)	150
Load Capacity / 4pcs (Kg)	600
Tyre Material	Polyurethane
Hub Material	Polyamide 6
Bracket Material	Pressed Stainless Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 80°
--	-------------

					
80x30	37	105	12	150	190

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	80
Wheel / Tread Width (mm)	30
Overall Height (mm)	105
Number of Fixing Holes	1
Fixing Hole Size (mm)	12
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	97
Levelling Extent (mm)	
Offset (mm)	37
Castor Weight (Kg)	0.448

Fixing Centres Specifications

Fixing Centres (mm)	
Fixing Centres Length (mm)	
Fixing Centres Width (mm)	

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	
Fixing Plate Length (mm)	
Fixing Plate Width (mm)	