

Model 340 (Dual Scale)



NorTorque[®] utilises Norbar's proven mechanism and internal components and built them into a purposeful and attractive torque wrench.

In developing NorTorque[®], Norbar's objective was to deliver outstanding quality and performance in a value for money package. Fine engineering ensures that the wrench adjustment is both fast and fingertip light meaning that you can do your job more efficiently.

Accurate to $\pm 3\%$ of reading which meets and exceeds ISO6789 with models available to cover 12 N·m to 340 N·m.

Part number: 130106

EAN Bar Code: 5060207565387

NATO number: 5120-99-6908519

Accuracy: $\pm 3\%$

Operates between:

60.0 - 340.0 N·m

45.0 - 250.0 lbf·ft



TECHNICAL SPECIFICATIONS

- Length: 679mm
- Weight: 1.55kg
- Ratchet Teeth: 60
- Square Drive: 1/2"
- Ratchet Diameter: 52mm

FEATURES

- Convenient hanger feature for tool storage also aids wrench unlocking and adjustment
- Just eight turns to cover the entire scale
- Micrometer scale applying to the primary torque units (N·m on a dual scale wrench) for simple and error free setting
- Accurate to $\pm 3\%$ of reading which meets and exceeds ISO6789
- Push/pull lock is fast and intuitive to use and prevents accidental adjustment of the set torque
- Light and fast adjustment saves operator time and effort
- Push through ratchets with a narrow engagement angle of 6° for working in tight space
- Each tool is supplied with a traceable calibration certificate