

3093 U-10

Reversible ratchet 3/8"

Code	ETIM
6236950	EC002218
EAN	UNSPSC
4010886623695	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



Article description

- Suitable for robust use in industry and commercial vehicles
- Acc. to DIN 3122, ISO 3315
- With lowered switch lever
- Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or anti-clockwise operation
- With push button release
- Return angle 11.25°
- Non-slip 2-component handle with suspension hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 10, ISO 1174, ball locking device
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Drive connector square (male)	3/8"
Net weight [kg]	0,254 kg	Drive connector square (male)	10 mm
Total length [mm]	200 mm	Return angle	11,25 °
Total width [mm]	35 mm	Handle material	2-components
Total height [mm]	30 mm	Ratchet head height	30,2 mm
Surface	chrome-plated	Locking type	Locking in middle position
Material	Chrome-vanadium steel 31CrV3	Push button release	yes
Standard	DIN 3122	Shift type	Changeover lever
	ISO 3315		