



PRODUCT-DETAILS

UPS PowerValue 11LI Pro 2000 VA

UPS PowerValue 11LI Pro 2000 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Pro 2000 VA
Product ID	4NWP100179R0001
EAN	7640169262692
Catalog Description	UPS PowerValue 11LI Pro 2000 VA
Long Description	VI UPS PowerValue 11LI Pro 2000VA/1400W;230V;50/60Hz;pure sinewave;3 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	9ac61ad0-bce7-4de2-90ab-ae59d8741c58 Switzerland
Simplified SCIP	398e6b57-8706-4591-a9bd-b6723b4460fd Germany 2fc58783-8e3b-4a59-995f-3879a910cf89 Germany 30ef323e-1f51-4c56-b41f-31a6eb23ae9b France f635ff1c-31cb-4b8b-a8d0-1ed0b1fdc15d Netherlands

6f9d26bd-428d-4070-9511-449f072469f1 Spain
dd13423d-5b88-4702-8876-b7f3f031056a Netherlands
0c2b9eda-ad0a-42b6-9d4b-be6e3475d17c Portugal
03cc50bf-f9fe-4ead-8ac3-9240a96810fa Bulgaria
7452218c-d31a-49c1-930e-1b5eb1166519 Sweden
91d47e9f-b402-409f-9265-bf81b152b6a3 France
ea7e4880-1cb9-4410-ae72-ec9477a1862f Poland
52657760-8644-44f5-9716-ea46e38b3e7b Sweden
c8ea79c1-efc7-4af6-bee8-c9b388caba31 Germany
1732bf89-6bbb-4239-a1b2-c1f82dd18327 Germany
438aa637-c8a8-44d6-ae34-6cb3daa18766 Poland
436ade6c-b436-41d3-b670-a320e0967b15 Norway
88f69724-41d7-49af-8394-90ca36955621 Finland
649aa4d0-a639-4e86-afc3-218b7a4263da Netherlands
3a691693-990e-41bb-b605-c5f564601da6 Germany
ca6e3cb8-5d35-43d2-bdef-eee31d648820 Denmark
784ca8b4-7926-4a9d-83b4-e64804f6d110 Croatia
1cb37075-9aef-4462-b11c-99caaa82573e Czech Republic
c415c712-9a39-4239-955b-9b7b89aaa751 Poland
72178fd6-7417-4881-a35f-a266b033de01 Netherlands
d979c121-50a3-4e28-9e81-55da12eb7817 Netherlands
12280d36-044a-4797-b89b-0c1b05bce20e Estonia
00e54354-e8af-4378-9551-910dc36e4d3a Greece

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408633
E-Number (Norway)	6600721
Country or Territory of Origin	China

Dimensions

Product Net Width	146 mm
Product Net Height	205 mm
Product Net Depth / Length	395 mm
Product Net Weight	11.9 kg

Container Information

Package Level 1 Units	box 1 piece
-----------------------	-------------

Package Level 1 Width	236 mm
Package Level 1 Height	297 mm
Package Level 1 Depth / Length	496 mm
Package Level 1 Gross Weight	14.2 kg
Package Level 1 EAN	7640169262692

Technical

Apparent Power Output	2000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.83 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Number of Batteries	2
Number of Outputs	C13 Connection 6
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	1200 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

