






- NOTES:
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
 - WILL ACCEPT SEVEN (7) TYPE XII PIN CONTACTS.
-  #4 FASTENER RECOMMENDED FOR MOUNTING.




DETAIL A

RECOMMENDED PANEL CUTOUT



DETAIL B

4-40 THREADED INSERTS	A	206137-5
.150±.003	B	206137-2
.150±.003	A	206137-1
DIM C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 05/31/94	 TE Connectivity	
		CHK W.G.LENKER 06/07/94		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
		0 PLC ± -	PRODUCT SPEC	
		1 PLC ± -	108-10024	
		2 PLC ± .005	APPLICATION SPEC	
		3 PLC ± -	—	
MATERIAL NYLON, BLACK		FINISH —	WEIGHT —	
		ANGLES ± -	A1 00779 206137	
			CUSTOMER DRAWING	