



Alphabetical Picture Part Number
SEARCH **SEARCH** **SEARCH**

Go To Step Search™ Screen


35184 -- *1 of 1 products*

Terminals and Splices
Ring and Spade Tongue Terminals

General **INFO**

Sales **INFO**

Customer Drawings
SPECIFICATIONS



Line art represents typical product only.

Searchable Features:

Terminal Shape	Ring Tongue
Body Style	SOLISTRAND
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Wire Range	2 [26.7-42.2 ²] AWG [mm]
Wire Range (CMA)	52,600-83,700
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	3/8 [9.53]
Stud Diameter	.375 [9.53] in. [mm]
Shape	RING-050
Heavy Duty	Standard
Packaging Method	Loose Piece
Material	Copper
Finish	Tin

Other Properties:

Dim. C	.531 [13.49] Min. in. [mm]
Dim. E	1.212 [30.79] Max. in. [mm]
Dim. L	1.657 [42.09] Max. in. [mm]
Dim. W	.890 [22.61] in. [mm]
Barrel I.D. Min.	.370 [9.39] in. [mm]
Stock Thickness	.073 [1.85] Max. in. [mm]