

2/2-WAY MAGNETIC VALVE



Specifications

| | |
|-------------------------------|---|
| Body Material | PPS |
| Flow Factor Kv | 0.005m ³ /h |
| Maximum Operating Temperature | +55°C |
| Maximum Working Pressure | 3bar |
| Minimum Operating Temperature | 0°C |
| Number of Ports | 2 |
| Orifice Diameter | 0.6mm |
| Suitable Applications | Aqueous Solution, Compressed Air, Water |
| Supply Voltage | 24 V dc |
| Type | 2/2 |