

4

3







2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - ,04FEB03

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FB	00	P		REVISED PER ECO-11-005033	26MAR11	RK HMR



TOLERANCES UNLESS OTHERWISE SPECIFIED:

10 ≥ * : ±0.2
30 ≥ * >10 : ±0.25
100 ≥ * >30 : ±0.3
ANGLE : ±3°

NOTES:
1.MATERIAL:
HOUSING: NYLON(G.F.) UL94V-0, COLOR: GRAY,BLUE
POST: PRE-TIN 0.5mm SQ. BRASS WIRE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S.YAO	31JAN03	TE Connectivity		
		CHK	S.YAO	31JAN03			
		APVD	T. SASAKI	31JAN03	NAME		
		PRODUCT SPEC			AMP Mini CT Connector 1.5mm Pitch		
		108 - 60018			Double Row Post HDR Ass'y (V)		
		APPLICATION SPEC			DIP Staggered Type with Boss with Kink		
		114 - 5223			SIZE	CAGE CODE	DRAWING NO
		WEIGHT			A3	00779	C-292208
		CUSTOMER DRAWING			RESTRICTED TO		
					SCALE	SHEET	REV
					-	1 OF 2	P

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

1.67	35.5	34.1	28.5	40	9-292208-0	4-292208-0
1.60	34.0	32.6	27.0	38	8-292208-8	3-292208-8
1.53	32.5	31.1	25.5	36	8-292208-6	3-292208-6
1.46	31.0	29.6	24.0	34	8-292208-4	3-292208-4
1.38	29.5	28.1	22.5	32	8-292208-2	3-292208-2
1.31	28.0	26.6	21.0	30	8-292208-0	3-292208-0
1.24	26.5	25.1	19.5	28	7-292208-8	2-292208-8
1.17	25.0	23.6	18.0	26	7-292208-6	2-292208-6
1.10	23.5	22.1	16.5	24	7-292208-4	2-292208-4
1.03	22.0	20.6	15.0	22	7-292208-2	2-292208-2
WEIGHT (g)	C	B	A	Pos.	BLUE	GRAY
	DIMENSIONS				PART NO	

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

By -

COPYRIGHT -



DIMENSIONS: mm	DWN —	MATERIAL —	FINISH —
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —	 TE Connectivity	
0 PLC ± — 1 PLC ± SEE SHEET 2 PLC ± 1 OF 2 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD —		
	PRODUCT SPEC —	NAME AMP Mini CT Connector 1.5mm Pitch Double Row Post HDR Ass'y (V) DIP Staggered Type with Boss with Kink	
	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779
	WEIGHT —	DRAWING NO C-292208	RESTRICTED TO —
CUSTOMER DRAWING		SCALE NON	SHEET 2 OF 2
		REV P	