



PRODUCT-DETAILS

MLBL-03R

MLBL-03R LED block



概要信息	
产品型号	MLBL-03R
产品ID	1SFA611621R1031
欧洲商品编号(EAN)	7320500544662
目录说明	MLBL-03R LED block
详细描述	The MLBL-03R LED block is: - Red - Illuminated - Front mounting - 60 V This LED block is part of ABB's modular plastic range, the most versatile range with a high level of flexibility and market-leading electrical ratings. Engineered for total reliability, longer lifetime, and highest mechanical durability. Self-cleaning contacts ensure reliable operation without the need for maintenance, increasing uptime. A high degree of protection guarantees reliability in extreme environments. The innovative design simplifies the entire process, from selection to easy and quick, tool-free installation. The perfect solution for every application.

订货信息	
最小起订量	10 piece
海关关税号	85369001

Popular Downloads	
数据手册，技术资料	1SFC151007C02__
说明书和手册	1SFC151011M0201

尺寸	
产品净宽	0.01 m
产品净高	0.044 m
产品净深	0.042 m
产品净重	0.01 kg

技术参数	
周围环境温度	Operation -25 ... +70 °C Storage -40 ... +85 °C
颜色	Red
照明	Illuminated
灯类型	60V AC / DC, integrated LED
安装类型	Front mounting
额定频率 (f)	50 / 60 Hz
额定工作电压	60 V AC/DC
连接容量	Flexible with Ferrule 1 x 0.75...2.5 mm ² Flexible with Ferrule 2 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 1 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 2 x 0.75...2.5 mm ² Flexible 1 x 0.75 ... 2.5 mm ² Flexible 2 x 0.75 ... 2.5 mm ² Solid 1 x 0.75...2.5 mm ² Solid 2 x 0.75...2.5 mm ²
连接类型	Screw Clamp
端子类型	Screw Terminals
拧紧力矩	0.9 N·m
剥线长度	8 mm
适用于	MCBH-00 MCBH5-00 MP1 MP2 MP3 MP4 MPMT3 MPMP3 M2SS1 M2SS2 M2SS3 M2SS4 M2SS5 M2SS6 M3SS1 M3SS2 M3SS3 M3SS4 M3SS5 M3SS6 M3SS7 M3SS8 MPM1
适用产品系列	Pilot Devices

UL/CSA适用的技术参数		
连接容量UL/CSA		1x 18...14 AWG
		2x 18...14 AWG

环境条件		
防护等级		Terminals IP20

Material Compliance		
Conflict Minerals Reporting Template (CMRT)		9AKK108467A5658
REACH Declaration		2CMT2022-006479
RoHS信息		2CMT2022-006498
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019	
Toxic Substances Control Act - TSCA		2CMT2023-006523
WEEE B2C / B2B		Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)	

认证及声明（文件编码）		
CB认证		SEMKO_SE-56219
CQC认证		CQC2008010305274953
cULus 认证		9AKK107046A9925
Declaration of Conformity - CCC		2020980305001106
符合性声明 - CE		2CMT2015-005452
Declaration of Conformity - UKCA		2CMT2020-006121
DNV GL Certificate		E-14107
EAC认证		1SFC150017D1101

包装信息		
1级包装单元		bag 10 piece
1级包装宽度		0.135 m
1级包装长度		0.155 m
1级包装高度		0.025 m
1级包装 总重		0.11 kg
1级包装 EAN		7320500372937

分类		
对象分类代码		E
ETIM 6	EC000204 - Lamp holder block for control circuit devices	
ETIM 7	EC000204 - Lamp holder block for control circuit devices	
ETIM 8	EC000204 - Lamp holder block for control circuit devices	
e级		V11.0 : 27371209
UNSPSC		39122221
IDEA 粒度分类代码 (IGCC)	5219 >> Switch part or accessory	

E-Number (Finland)	2315755
E-Number (Sweden)	3705615

分类

低压产品及系统 → 控制产品 → 按钮指示装置 → Accessories
低压产品及系统 → 控制产品 → 按钮指示装置 → 按钮和指示灯
中压产品与系统 → 服务业务 → 备件 → Parts → All Spare Parts (Relays-SWG-CB)

