



AERMLED2/120/DL



Features

High performance maintenance free LED panel

TPa as standard

60W panel outperforms 3x28W T5

Cool white, warm white and daylight options

White anodised aluminium frame for visual compatibility with ceiling grid

Low glare and even light distribution for multiple applications

Panel Pod Self-Test emergency option

Panel Pod sensor option

Powered by Philips

LED lifespan L80 B10 54,000 hours

General Information

Lamp Type	LED
Colour / Finish	White
IP Rating	IP44
Class Protection	2
Internal / External	Internal
Surface / Recessed / Suspended	Surface/Recessed/Suspended
Diffuser Rating	Tp(a)
Warranty (Years)	5
CE Mark	Yes
Length (mm)	1195
Width (mm)	595
Height (mm)	10
Accessories	AERMLED/SK, AERMLED/120/SMF

Technical Information

Wattage	58W
Lumens Delivered	5646lm
Lm/W	97lm
CRI	Ra 80
CCT	6500K
Input	230V
Hertz	50/60Hz
Operating Temp	-20°C to 40°C

Datasheet generated from <https://onetimepim.com> last updated Monday, June 28, 2021 11:59:34 AM