

Han 24HPR-HTE-M25-break-away




Image is for illustration purposes only. Please refer to product description.

Part number	19 40 024 4421
Specification	Han 24HPR-HTE-M25-break-away
HARTING eCatalogue	https://harting.com/19400244421

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Hood
Features	Corrosion resistance ASTM B117-09 (500 h)

Version

Size	24 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Break-away
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP69K IP65 / IP68

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	Silicone



Pushing Performance
Since 1945

Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61373
	IEC 60529
	EN 45545

Commercial data

Packaging size	1
Net weight	611 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140285163
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466