



NHS-4.8-0-5M

SHRINK TUBE WITHOUT ADHESIVE, 2:1, ID=4.8mm BLACK, L=5m, THIN-W



Product Properties:

Model	Thin-walled
Operating temperature	-55-125 °C
Transparent	No
Type	Heat-shrink
Shrink rate	2:1
With inner glue	No
Printable	No
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	No

Dimensions:

Wall thickness after shrinking	0.55 mm
MOQ	1 .
Unit	pck
Length	5 m
Nominal diameter inch	3/16 inch
Inner diameter before heat-shrink	4.8 mm
Inner diameter after heat-shrink	2.4 mm

Approvals:

Approved according to cURus	Yes
UL approval	No

Approved according to CE	Yes
Approved according to CSA	Yes

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	Compliant
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000217 - Shrink tubing
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Retailer Concepts & Assortments
Alternative SKU	NHS-4.8-0-5M

Logistic information:

Barcode	733117613296
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	NHS-4.8-0-5M
Taric code	39173200
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.