

ToLEDo SUPERIA T5 AC V2 5FT 5600LM 840

Item No: 0029260




50,000 hours average rated lifetime Last 2.5 times longer than 80W 1449mm fluorescent tri-phosphor T5 lamp High switching cycles - 200,000X Omni-directional light distribution and wide beam angle Minimum and maximum operating temperature: -20°C to 50°C Glass construction and polycarbonate end-caps Only suitable for direct mains (AC 220-240V) operation Ideal for factories, parking lots, supermarkets, department stores, schools and offices Not suitable for operation with electronic/ECG or magnetic/CCG ballasts

Technical Assets

Dimensions (mm)

Photometrics



ToLEDo SUPERIA T5 AC V2 5FT 5600LM 840

Item No: 0029260



General data

Product name	ToLEDo SUPERIA T5 AC V2 5FT 5600LM 840
Technology	LED
Watt (Rated) (W)	37
Lamp shape	Tube, double-ended
Cap/Base	G5
Lamp finish	Opal
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Residential & Consumer
Operating temperature range (°C)	-20°C...+45°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4941334
Warranty	5 years

Optical data

Useful luminous flux (Φuse)	5600
Luminous flux (Rated) (lm)	5600
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	150
Photobiological Risk Group	RG0
Lumen maintenance at end of nominal life (%)	70

Electrical data

Power consumption (W)	37
Wattage (W)	37
Primary Supply/Product voltage - min (V)	220
Primary Supply/Product voltage - max (V)	240
Lamp power factor	0.9
Control gear required	No
No. Of switching cycles before premature failures	>100000
Dimmable	No
Inrush Current (A)	24.4
Inrush Duration (µs)	13
Lamp Energy Label (class)	D
Max. products per 16A C Breaker	52
Max. products per 16A B Breaker	52

Lifetime data

Lifespan L70 B50	50000
Average life (Nominal) (h)	50000
Average life (Rated) (h)	50000

Physical data

IP rating	IP20
Nominal Product Length (mm)	1462
Nominal Product Diameter (mm)	17
Weight (kg)	0.17

ToLEDo SUPERIA T5 AC V2 5FT 5600LM 840

Item No: 0029260



Packaging

Product EAN number	5410288292601
Packaging single length / height (cm)	146.2
Packaging single width (cm)	1.8
Packaging single depth (cm)	1.8
DUN14 (inner)	15410288292608
Units per outer package	10
Packaging outer length / height (cm)	152.1
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	7.8

Safety data

Optimal operating condition (°C)	-20-45
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Suitable for household illumination	Yes
Safety message	Suitable for totally enclosed fixture