

Datasheet

RS Pro Steel Alloy Compression Spring, 71mm x 14.5mm, 6.69N/mm

RS Stock No: **121-264**



Product Details

RS Pro stainless steel alloy compression spring measures 71 x 14.5 mm and has a spring rate of 6.69 N/mm. It handles a load of 253.99 N at a minimum working length of 33 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Ground
Material	Steel Alloy
Free Length	71 mm
Load at Minimum Working Length	253.99 N
Minimum Working Length	33 mm
Outside Diameter	14.5 mm
Spring Rate	6.69 N/mm
Wire Diameter	2 mm