



Pushing Performance
Since 1945

UICIT_WMRF 8_DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 008 1033
Specification	UICIT_WMRF 8_DUMMY KIT
HARTING eCatalogue	https://b2b.harting.com/09580081033

Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC IT
Element	Connector sets
Specification	Dummy kit

Version

Gender	Female
--------	--------

Technical characteristics

Insulation resistance	$>10^7 \Omega$
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-40 ... +90 °C
Mating cycles	$\geq 10,000$
Degree of protection acc. to IEC 60529	IP67 / IP69

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 6005 (moos green)



Pushing Performance
Since 1945

Material properties

Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	0.657 kg
Country of origin	India
European customs tariff number	85366990
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)