

2 Port HDMI Video Splitter with Audio - USB Powered

Product ID: ST122HDMILE



The ST122HDMILE 2-Port HDMI® Video Splitter with Audio lets you share a single high definition video and audio source between two HDMI or DVI (with HDMI to DVI cable) displays. The HDMI splitter is USB-powered, making it ideal for use with desktop and laptop computers that offer HDMI output.

The USB powered High Speed HDMI splitter is HDCP 1.1 compliant, delivering outstanding audio capability and flawless digital video at resolutions of up to 1080p.

To overcome connection distance limitations, the HDMI splitter also functions as an HDMI distribution amplifier allowing you to situate HDMI monitors up to 45ft (15m) away from the HDMI source - a perfect solution for connecting an HDMI-capable computer to monitors, projectors or plasma screens as needed.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connecting multiple HDMI® enabled projectors, LCD Displays, and Plasma Displays from a single PC source
- Ideal for classroom settings, where educators can display their computer screen on multiple displays for better visibility
- Perfect for corporate boardrooms that employ multiple screens or projectors
- Set up your trade show display with multiple screens
- Use in retail environments for advertising or training

Features

- Splits an HDMI® source to 2 outputs, without signal loss
- Integrated signal amplifier - situate displays up to 45ft(15m) away
- Supports a wide range of HDTV resolutions, from 480p to 1080p
- USB-powered - no wall outlet or bulky power supply required
- High Speed HDMI® and HDCP 1.1 compliant
- Compact design

Hardware	Warranty	2 Years
	AV Input	HDMI
	AV Output	HDMI
	Daisy-Chain	Yes
	Industry Standards	High Speed HDMI®, HDCP
	Ports	2
Performance	Maximum Cable Length	15 m [49.2 ft]
	Supported Resolutions	480p, 480i, 720p, 1080i, 1080p 1600x1200(UXGA)
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI (19 pin) Male 1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	2 - HDMI (19 pin) Female
Special Notes / Requirements	System and Cable Requirements	An HDMI source (desktop / laptop) with a USB port for powering ST122LE.
Indicators	LED Indicators	1 - Power
Power	Input Current	500mA
	Input Voltage	5 DC
	Power Source	USB-Powered
Environmental	Humidity	0~95% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Physical Characteristics	Cable Length	280 mm [11 in]
	Color	Black
	Enclosure Type	Plastic
	Product Height	2.5 cm [1 in]
	Product Length	75 mm [3 in]
	Product Width	50 mm [2 in]
	Weight of Product	76 g [2.7 oz]
Packaging Information	Package Height	40 mm [1.6 in]
	Package Length	21 cm [8.3 in]

	Package Width	14.5 cm [5.7 in]
	Shipping (Package) Weight	219 g [7.7 oz]
What's in the Box	Included in Package	1 - HDMI Splitter 1 - 24" USB Power cable 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.