



hp jornada 560 series



data sheet

Meetings, appointments, projects, and deadlines - sometimes its hard to keep it all together. Organizing isn't the issue - it's about doing more on the go. The HP Jornada 560 series personal digital assistants have everything you need to gracefully juggle the details and have fun while you're doing it. They are designed to address the needs of the mobile business professionals who demand the most powerful Pocket PC with top of the line features...all in a 173g stylish magnesium casing !

perform

- work longer - up to 14 hours battery life* with the included battery pack
- powered by a 206 MHz StrongArm processor for high performance
- with 32 MB RAM (jornada 565) or 64 MB RAM (jornada 568), and 32MB flash ROM, you have all the room you need to load more applications and store more contacts
- add the memory you need, the accessories you want with the built-in CompactFlash™ Type I extended slot
- double battery life with the optional battery (not included, sold separately)
- recharge at home or in office - just plug in the AC adapter
- instantly access the information you need using four quick-launch keys and navigation pad

get connected

- browse the web**, check e-mails, connect with other compatible PDAs, PCs, and more...
- work with the mobile versions of the Microsoft® programs you use the most - Pocket PC versions of Outlook, Word and Excel
- multi-task - work on a Word document while listen to your favorite MP3's
- synchronize with your desktop PC at the touch of a button, using USB or serial connectivity (purchase serial connectivity accessories separately)
- stay connected and productive with the hp jornada 560 series connection card adapter (not included, sold separately)

color, clarity and style

- the vibrant, reflective, 16-bit colour display gives you a clear view both indoors and outdoors
- view and share digital photos using included software with the HP pocket camera (accessory sold separately)
- lightweight and durable hard cover with a sleek design for easy handling

* With backlight off, estimated battery life. Actual battery life will vary based on usage.

** Internet use requires a modem or LAN card purchased separately; connect time charges may apply. Some website/web content may be unavailable. Check with your service provider for availability in your area.

HP Jornada 560 series personal digital assistant

technical specifications

Part Number

F1865A - hp jornada 565
F2915A - hp jornada 568

Processor

206 MHz 32-bit StrongARM processor

Memory

32 MB RAM (Jornada 565), 64 MB RAM (Jornada 568)
32 MB Flash ROM
103 MHz memory data bus

Display

240 x 320 pixels 3.5 in color Reflective TFT LCD
Up to 16 bits (65,536 colors)

Standard Features

USB cradle
LEDs (appointment notification, charging status)
Record button
4-hot keys
Side Up/Down buttons
Navigation pad

Power

Removable, rechargeable Li-Polymer battery pack
14-hours of battery life (with backlight off, estimated battery life, actual battery life will vary based on usage)
1- 3V coin-cell back-up battery
AC adapter (multi-voltage)

Input/Output

One IrDA infrared port
One USB (Slave)/serial RS232C
AC input jack
Earphone jack
Expansion slot: One CompactFlash™ Type I extended

Sound

Audio speaker
Microphone
Built-in voice recorder
Digital audio player compatible

Other Standard Features

USB cradle
AC adapter

Physical Specifications

5.20 x 3.01 x 0.68 in. (132 x 76.5 x 17.2 mm)
6.1 oz (173g) with standard battery (without cover)

Operating Requirements

Operating temperature: 32 - 104° F (0 - 40° C)
Storage temperature: 32 - 131° F (0 - 55° C)
Humidity: up to 90% relative humidity at 104° F (40° C)

Software included in ROM

Microsoft® Pocket PC Software 2002 (Premium Edition) includes:

Microsoft® Windows® for Pocket PC¹
Pocket Outlook® (manage calendars, tasks, and contacts)¹
Pocket Internet Explorer® plug-in for AvantGo™ (browse Web pages, AvantGo Mobile Channels, Mobile Favorite Synchronization, Microsoft Mobile Channels)
Pocket Word and Excel (view and edit Word and Excel documents)¹
Microsoft Reader 2.0 for Pocket PC (read electronic books)²
Windows Media™ Player 8 for Pocket PC (enjoy digital music)¹
MSN Messenger¹
Terminal Services Client¹
Note Taker¹
Voice Recorder¹
ActiveSync™ 3.5¹
Calculator¹
Solitaire¹
File Explorer¹
hp jornada settings¹, backup¹, home menu¹, task switcher¹, Microchai², image viewer (for image viewing and slideshow)¹
LandWare Omnisphere™ 1.01 (business and financial calculator)¹
CodeWallet Pro v3⁴
Access Panel Platinum³

HP/Microsoft Pocket PC companion CD-ROM includes:

Microsoft software:
ActiveSync™ v3.5¹
Internet Explorer (desktop version)¹
Microsoft Outlook 2002 (full retail desktop version)¹
Microsoft Pocket Money for Pocket PC² (manage your stocks and check account)
Microsoft Reader for Pocket PC² and PC²
Microsoft Reader eBooks³
Microsoft Pocket Streets⁴
Microsoft Transcriber⁴
Windows Media Player for Pocket PC¹ and PC²

HP software:

MusicMatch® Jukebox 6.0 (internet radio, record, organize and play digital music)⁵
AudiblePlayer™ 2.0 for Windows and Pocket PC and AudibleManager™ 3.0 (listen to audiobooks and news)³
PhatWare™ HPC Notes™ 3.05 Lite and Professional Trial (create and organize notes)³
Microchai²
user manual¹

¹ English, French, Italian, German, Spanish and Portuguese

² English, French, Italian, German and Spanish

³ English only

⁴ English, French and German

⁵ English, French, German and Spanish

Warranty

One-year limited warranty

ordering information

F1865A

What's in the box

HP Jornada 565 personal digital assistant, ac adapter, USB cradle, user's guide, quick start card, accessories guide, regulatory and warranty information, 3V CR2032 coin cell back-up battery, Pocket PC Companion CD.

F2915A

What's in the box

HP Jornada 568 personal digital assistant, ac adapter, USB cradle, user's guide, quick start card, accessories guide, regulatory and warranty information, 3V CR2032 coin cell back-up battery, Pocket PC Companion CD.

jornada 560 series accessories

Number	Description
F2901A	Standard battery pack
F2922A	A/C adapter - multi-voltage
F2902A	Leather case
F2903A	USB cradle
F2904A	Serial cradle
F2906A	Stylus pens
F2911A	Pocket keyboard
F1869A	HP pocket camera
F1839A	Pretec modem
F1838A	Psion modem
F2900A	Car/DC adapter
F2926A	USB cable
F1819A	Serial cable
F2923A	Leather clip-on pouch
F2909A	Extended battery pack
F2912A	PC Card Adapter
F2913A	Battery w/MMC expansion
F1888A	Targus Stowaway keyboard
F2925A	SmartCard battery pack
F2905A	Dual slot charging cradle
F2907A	Accessory cover



Targus Stowaway portable keyboard:
F1888A



Leather case:
F2902A



Pocket camera:
F1869A

for more information

Visit us on the world wide web at www.hp.com/eu/jornada



Microsoft, Windows and ActiveSync are registered trademarks of Microsoft Corporation in the United States and/or other countries. OmniSolve is a trademark of LandWare, Inc., MusicMatch is a registered trademark of MusicMatch Corporation. AudiblePlayer and AudibleManager are trademarks of Audible Inc. HPC Notes and PhatWare are trademarks of PhatWare Corporation.

All other brand and product names are trademarks or registered trademarks of their respective companies.

In a continuing effort to improve the quality of our products, technical and environmental information in this document is subject to change without notice.