

Features

- Suitable for panel/wall mounting or window mounting with appropriate window accessory kit
- Simple installation
- External 2 speed reversible on/off controller available
- Manufactured impact resistant high gloss ABS for strength and durability
- Motor fitted with thermal over load protection

RS PRO 300mm Commercial Fan with Fixed Grille

RS Stock No.: 221-3564



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- 300mm fixed grille fan suitable for panel/wall mounting or window mounting using the appropriate window accessory kit. Suitable for commercial applications in pubs, hotels, restaurants, offices, schools, shops and factories.
- Double Insulated, class II motor fitted with thermal protection
- IP44 rated, DEMKO Approved, and CE marked in accordance with all the relevant EEC Harmonised Directives.
- Meets the requirements of Building Regulation Document F
- Panel Mount Airflow: 267l/sec
- Window/Wall Mount Airflow: 415l/sec

Mechanical Specifications

Hole Diameters:	Window 337mm, Wall 357mm
Height	340mm
Width	340mm
Depth	158mm

Electrical Specifications

Rated Voltage	220-240v-50Hz
Rated Wattage	90w

Protection Category

IP Rating	IP44
-----------	------

Accessories

Window Kit
Speed Controller