

DX430 - DX4 Hi-Vis Class 2 Winter Jacket

Collection: DX4

Range: High Visibility

Shell Fabric: Portwest Extreme Waterproof: 100% Polyester Stretch, 150D, PU Membrane

Outer Carton: 8

Product information

Fresh dynamic design combined with superior stretch breathable fabric make this the most desired high visibility winter jacket on the market. Packed full of innovative features including HiVisTex Pro heat applied reflective tape, Texpel Splash water resistant finish, brushed micro fleece collar, and articulated sleeves. The superior InsulatexPro padded insulation gives perfect warmth without adding unnecessary weight. This jacket is guaranteed to make the wearer look great while keeping them safe and comfortable no matter what the task.

DX4

Stretch your limits with Portwest's dynamic workwear collection. This contemporary collection combines all the technical features required of modern workwear, with many clever innovations to ensure the wearer achieves maximum function and style. The DX4™ collection combines high performance stretch fabrics with robust oxford panels to provide unparalleled ease of movement and supreme flexibility. What defines this collection is the cutting edge designs which allow for a full crossover from work to leisure activity.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 343 Class 4:1 X (WP 20,000MM)
EN 342 (0.334 (M².K/W), 3, X)



Features

- Premium waterproof and breathable fabric with mechanical stretch properties
- Waterproof with taped seams preventing water penetration
- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- EN342 Protection against cold certified up to -40°C
- InsulatexPro lining offers superior warmth without adding unnecessary weight
- Vertical and horizontal hood adjustment for customisable fit
- Drawcord adjustable hem
- Dropped back hem for better coverage
- Zipped chest pockets
- Two lower pockets
- Internal chest pocket

DX430 - DX4 Hi-Vis Class 2 Winter Jacket

Commodity Code: 6201409019

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)

SATRA Technology Park

NN16 8SD, United Kingdom

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
DX430OBRS	Orange/Black	60.0	40.0	40.0	0.9990	0.0960	5036108412105	15036108897626
DX430OBRM	Orange/Black	60.0	40.0	40.0	1.3470	0.0960	5036108412099	15036108897619
DX430OBRL	Orange/Black	60.0	40.0	40.0	1.3930	0.0960	5036108412082	15036108897602
DX430OBRXL	Orange/Black	60.0	40.0	40.0	0.9990	0.0960	5036108412112	15036108897633
DX430OBRXXL	Orange/Black	60.0	40.0	40.0	0.9990	0.0960	5036108412129	15036108897640
DX430OBRXXXL	Orange/Black	60.0	40.0	40.0	0.9990	0.0960	5036108412136	15036108897657
DX430OBR4XL	Orange/Black	60.0	40.0	40.0	0.9990	0.0960	5036108412075	15036108897596