

Ferrite Shallow Pot Magnets (Zinc Plated)



The blind ended shallow pot magnet is meant for press fitting into an application (so it does not require holes or threads to connect to it). The blind ended shallow pot magnet can sometimes also be used for applications where it clamps to a ferromagnetic surface and it is not meant to be easily removed (it is deliberately meant to be difficult to get a hold of for trying to remove).



- For press fitting applications
- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body

RS PART NO	ECLIPSE PART NO	PULL FORCE (KG)	Dia (mm)	Height (mm)	Weight (kg)	DESCRIPTION
9175670	E700	0.4	10	4.5	0.002	10mm Ferrite Shallow Pot Magnet
9175673	E701	1.0	13	4.5	0.003	13mm Ferrite Shallow Pot Magnet
9175677	E702	1.8	16	4.5	0.0045	16mm Ferrite Shallow Pot Magnet
9175686	E703	3.0	20	6	0.010	20mm Ferrite Shallow Pot Magnet
9175689	E704	4.0	25	7	0.019	25mm Ferrite Shallow Pot Magnet
9175683	E705	8.0	32	7	0.030	32mm Ferrite Shallow Pot Magnet
9175692	E706	12.5	40	8	0.055	40mm Ferrite Shallow Pot Magnet
1314781	E707	22	50	10	0.10	50mm Ferrite Shallow Pot Magnet

All sizes and colours available from stock. Please get in touch for further information.

Eclipse Magnetics, Atlas Way, Sheffield, S4 7QQ, England
T +44(0)114 225 0613 info@eclipsemagnetics.com
F +44(0)114 225 0610 www.eclipsemagnetics.com