



Product data sheet

Power tools for trade & industry

EXACT 12V-6-670

INDUSTRIAL EXACT 12V-6-670



Smaller, shorter, lighter – The most ergonomic production screwdriver!

The most important data

Torque (hard)	1.5 – 6 Nm
Speed	134 – 670 rpm

Part Number 0 602 496 400

Technical data

Technical data

Torque, from (hard)	1.5 Nm
Torque, to (hard)	6 Nm
Torque (hard)	1.5 – 6 Nm
Torque, from (soft)	1.5 Nm
Torque, to (soft)	6 Nm
Torque (soft)	1.5 – 6 Nm
Speed, from	134 rpm
Speed, up to	670 rpm
Speed	134 – 670 rpm
Direction of rotation	R/L
Weight	0.66 kg
Comment	No load speed with Power Boost up to 900 rpm. Below 50% speed setting eventually lower power. Machine capability testing is done at 600 rpm according to VDI 2647. Changes to the tool speed and torque may also affect accuracy. Please verify machine capability at your specific setting.

Bit holder	1/4" quick change chuck
Battery	GBA 12V
Drive type	Battery
Design	Centre grip
Connector type	Shut-off clutch

Noise/vibration information

Screwdriving

Vibration emission value ah	0 m/s ²
Uncertainty K	1.5 m/s ²

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

