



ENGLISH

Datasheet

RS Pro 1/4in Through Hole Stereo Jack Socket, 3A

RS Stock No: 449-348



Product Details

RS Pro stereo jack socket measuring 1/4 Inch, is designed for quality contact performance and durability, coupled with a competitive price structure. This heavy duty nylon bodied socket has plastic threaded nose and nut for security to panel. The through hole socket with 3 A current rating, has solid nickel silver switched contacts. Recommended nose mounting hole diameter is 11.2 mm and maximum panel thickness 3.1 mm.

Features and Benefits

- Recommended nose mounting hole diameter of 11.2 mm
- Maximum panel thickness of 3.1 mm
- Current rating of 3 A

**Specifications:**

Body Orientation	Straight
Colour	Black
Contact Material	Brass
Contact Plating	Silver Over Nickel
Current Rating	3 A
Gender	Female
Housing Material	Nylon
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-25°C
Mounting Type	Through Hole
Size	1/4 in
Termination Method	Solder
Type	Stereo Jack Socket
Voltage Rating	50 V
Contact Resistance	<15 to 30 mΩ