

Floor standing polyester enclosure, PanelSeT PLA, plain door, ventilated canopy, 750x1250x320mm, IP44, IK10

NSYPLAT7123G

Main

PanelSeT	
PanelSeT PLA	
Multi-purpose	
Suitable enclosure	
PLAT	
750 mm	
1250 mm	
320 mm	
Floor-standing	
1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy	

Complementary

Body type	Open top and sealed bottom part assembled with side parts	
Door type	Plain front	
Number of doors	2 door(s)	
Door opening side	Right and left (120 °)	
Lock type	2 points handle lock, 5 mm double-bar	
Accessibility for operation	Front Rear Top	
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element	
Material	Polyester reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product certifications	Veritas	
Electrical insulation class	Class II	

Environment

IP degree of protection IP44 conforming to IEC 60529 (with ventilated canopy)

IK degree of protection	IK10 conforming to IEC 62262 (plain door)		
Fire resistance	960 °C conforming to IEC 62208		
Ambient air temperature for storage	-3590 °C		

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	38.500 cm
Package 1 Width	80.000 cm
Package 1 Length	129.000 cm
Package 1 Weight	40.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	4
Package 2 Height	172.000 cm
Package 2 Width	100.000 cm
Package 2 Length	130.000 cm
Package 2 Weight	171.000 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	311
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Packaging	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No