



Hand protection

VENICUTF07

INTENSE CUT WORK

Level F cut-resistant glove, ideal for oily or aqueous environments, with good grip thanks to a granular nitrile coating



Specific benefits



Easy to use

• Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use



Hygiene

• Nitrile means no risk of allergies for users



Cost-effective

• User-friendly worksite package, including three pairs for weekly use

Technologies & labels

• EConocut

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Maintenance
- Automotive

Certifications and norms



EN 388

4 3 4 3 F

ANSI ISEA 105

A6

Protects against risks



Cutting



Wearing



Hand protection

VENICUTF07

INTENSE CUT WORK

Level F cut-resistant glove, ideal for oily or aqueous environments, with good grip thanks to a granular nitrile coating

Standards - Details



EN388:2016+A1:2018

4 [0-4] ABRASION RESISTANCE
3 [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
3 [0-4] PIERCE RESISTANCE
F [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Coating material and finition	Grip-textured nitrile
Coating level	Palm coated
Number of layer	Single layer
Gauge	13
Color	Grey-Black
Size	7, 8, 9, 10, 11
Type of packaging	Pack of 3



Safety gloves

VENICUTF07

INTENSE CUT WORK

Level F cut-resistant glove, ideal for oily or aqueous environments, with good grip thanks to a granular nitrile coating

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VECUTF07GRG307	Grey-Black	07	VENICUTF07	3295249296568	13295249296565	40	4	0.0 kg	30.5 cm	60.0 cm	38.5 cm
VECUTF07GRG308	Grey-Black	08	VENICUTF07	3295249296575	13295249296572	40	4	0.0 kg	61.0 cm	31.0 cm	38.5 cm
VECUTF07GRG309	Grey-Black	09	VENICUTF07	3295249296582	13295249296589	40	4	0.0 kg	30.0 cm	56.0 cm	37.0 cm
VECUTF07GRG310	Grey-Black	10	VENICUTF07	3295249296599	13295249296596	40	4	0.0 kg	30.5 cm	61.0 cm	39.0 cm
VECUTF07GRG311	Grey-Black	11	VENICUTF07	3295249296605	13295249296602	40	4	0.0 kg	36.0 cm	54.0 cm	27.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height