





CABLE TIE 50LB 11 NAT NYLON 2-PC D

__

General Information

Extended Product Type	TY5253M
Product ID	7TAG009180R0006
EAN	5414363065562
Catalog Description	CABLE TIE 50LB 11 NAT NYLON 2-PC D
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 289.7mm (11.40 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

Ordering

EAN	5414363065562
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.006 lb
	2.721 g

Container Information

Package Level 1 Units	100 piece	
Package Level 2 Units	500 piece	
Package Level 2 Width	5.25 in	
	133 mm	
Package Level 2 Height	5.75 in	
	146 mm	
Package Level 2 Depth / Length	15.25 in	
	387 mm	

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.138 to 3.07 in
	3.5 to 78 mm
Color	Natural
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6

TY5253M 2

Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Surface Finishing	Untreated
Tensile Strength	50 lb 222 N
Thickness	0.055 in 1.4 mm
UPC	786210869896

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY5253M
Instructions and Manuals	TY5253M

Classifications

IDEA Granular Category Code (IGCC)	5034 >> Cable ties
WEEE Category	Product Not in WEEE Scope
UNSPSC	39121703
ETIM 7	EC000046 - Cable tie
ETIM 6	EC000046 - Cable tie

Categories

 $Low\ Voltage\ Products\ and\ Systems\ \rightarrow\ Installation\ Products\ \rightarrow\ Wire\ Management\ and\ Connectivity\ \rightarrow\ Cable\ Ties$

