

Features

- 5.08 mm pitch
- Voltage Rating: 300V
- Current Rating: 12A
- Low Mating Force
- Low Profile
- 4 WAY SCREW TERMINAL WITH FLANGE

RS PRO 5.08MM PITCH, 4 WAY, 12A SCREW TERMINAL WITH FLANGE

RS Stock No.: 0631120



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Right angle cable mount terminal block plug connectors with a 5.08 mm pitch, M2.5 screw flanges and a 300V 12A electrical rating. These 5.08mm cable mount pluggable terminal blocks have M2.5 rising cage clamp screw terminals. They accept a wire size range of 28 AWG to 12 AWG and green PA66 housings.
- Standard accepts wire 28-12AWG 2.5 mm²

General Specifications

Number of Contacts	4
Number of Rows	1
Pitch	5.08mm
Mounting Type	Through Hole
Body Orientation	Straight
Number of P	4
Termination Method	Screw (M2.5, Steel(A3), Zinc Plated
Clamp	Phosphor Bronze, Nickel Plated
Wire Cage Material	Brass (Nickel Plated) or Steel (Zn Plated)
Housing	PA66 (UL94V-0)
Colour	Green

Electrical Specifications

Voltage Rating	300V
Current Rating	12A
Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	5.08 mm
Pin size	Please see below drawings

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

Spec Drawings

